










Article list no. 17


Description	Access- sory for:	Picture
<p>Particle Counter PZG for Gas and Air:</p> <ol style="list-style-type: none"> PZG 31/51 (0.3/0.5 µm, 28.3 LPM) PZG 21 (0.2 µm, 28.3 LPM) PZG 131 / 151 (0.3/0.5 µm, 100 LPM) <p>Included: Operation manual, power cable, battery (optional), isokinetic sample probe with 3 m antistatistical tube, purge filter, USB-stick, thermal printerpaper, calibration certificate</p>	---	
<p>A250 Aerosol Generator</p> <p>Included: Operation manual, calibration certificate, main-adapter, 100 ml glass container with locking-screw, aerosol-nozzle with PVC-hose</p>	---	
<p>V100 Dilution System</p> <p>Included: antistatistical tube to connect the particle counter, operation manual, calibration certificate</p>	---	
<p>Impaktor FH 6</p> <p>Included: calibration certificate, operation manual, battery charger</p>	---	
<p>FOG 2010 Fog Generator</p> <p>Included: 3 m flexible power cord, tank holder, tank bottle with suction hose and filter, instruction manual, external tank lid (canister) with suction hose, remote control, hose, hose adaptor for ducting hose</p>	---	

Article list no. 17		
Description	Accesso- ry for:	Picture
<p>Case</p> <p>For accommodation and protection of the device. Interior completely upholstered with dense foam</p>	A250 + V100, FH6	
<p>Case for PZG</p> <p>For accommodation and protection of the device. Interior completely upholstered with dense foam</p>	all PZG	
<p>PZG Diffuser</p> <p>Measuring range: appr. 1.3 – 9.8 bar Material: aluminium / steel / epoxy Measure: appr. 30.5 cm</p>	PZG (28.3 l/min)	
<p>Measuring Funnel</p> <p>630 x 630 mm incl. telescope rod</p>	PZG	
<p>Sampling pistol for external start and stop</p>	all PZG	
<p>Isokinetic Sample Probe round</p> <p>a) without cap, chromium-plated b) with cap, chromium-plated c) without cap, inox</p>	PZG (28.3 l/min)	

Article list no. 17

Description	Access- sory for:	Picture
Inox Holding Device for isokinetic sample probe High appr. 23.5 cm (Delivery without isok. sample probe)	PZG (28.3 l/min)	
Isokinetic Rectangle Sample Probe Innen: 80 x 15 mm; außen: 82 x 17 mm	PZG (28.3 l/min)	
Sampling tripod with rollers extendable up to 4 m in height	all PZG, Impaktor FH6	
Table Sampling Tripod height-adjustable 33 – 85 cm	all PZG	
Thermal paper	all PZG	
DEHS Di-Ethyl-Hexyl-Sebacat filled in bottle sizes: 0.1 l 0.5 l 1.0 l 5.0 l	A250	

Article list no. 17

Description	Accessory for:	Picture
Holding clamp with suction foot for run-off nozzles	A250	
Additional bottle with screw-on cap	A250	
Remote Control	FH6	
Fog Fluid „Extra Clean“ special fog fluid for air flow detection in pharmaceutical clean rooms	FOG 2010	
Technical Fog directing Injection-Nozzles to be screwed on to the heated nozzle attachment at the outlet (6 mm Ø x 200 mm long): Straight fog injection nozzle Arch type fog injection nozzle Right-angled fog injection nozzle Hooked fog injection nozzle (100/100mm long)	FOG 2010	